



NVSZMFG01ABG - NV2 Series, Gray Non-Metallic Medium Flashing Xenon Lt Fixt (Lamp Incl), 3/4" Wall Mount w/ Amber Strobelight & Guard, 120VAC, 50/60Hz

By Killark
Catalog # [NVSZMFG01ABG](#)



NV2 Series - Gray Non-Metallic Corrosion Resistant Medium Flashing Xenon Light Fixture (Lamp Included) - 3/4 Inch Wall Mount With Amber Strobelight And Guard - 120VAC At 50/60Hz.

Features

Designed for indoor and outdoor applications

General

Catalog Number	NVSZMFG01ABG
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Flashing
Light Source	
Material	Polyester, Fiberglass Reinforced
Mounting Type	
Optic Type	Polycarbonate Globe - Amber
Series	NV
UPC	783936071213

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120 VAC

Certifications And Compliance

Hazardous Rating(s)	Class I, Division 2, Groups A, B, C, D Class I, Zone 2, Groups IIC, IIB, IIA Class II, Division 2, Groups F, G Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

[Certifications - NVSL & NVSP Series CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand