



NVZMFG26RBG - NV2 Series, Gray Non-Metallic Medium Flashing Xenon Lt Fixt (Lamp Incl), 3/4" Wall Mount w/ Red Strobelight & Guard, 12-80VDC/24VAC

By Killark
Catalog # [NVZMFG26RBG](#)

NV2 Series - Gray Non-Metallic Corrosion Resistant Medium Flashing Xenon Light Fixture (Lamp Included) - 3/4 Inch Wall Mount With Red Strobelight And Guard - 12-80VDC/24VAC

Features

- NVSZ Series Xenon with 10,000 hours expected life flashing only.
- Available in five colors colors - red, green, amber, blue and clear.
- Xenon flash rate 60 to 80 per minute
- Can be mounted in any orientation including lens in the UP or SIDE positions.
- Materials: High strength 30% glass-filled thermoset polyester body with Lexan® lens. Resists corrosive effects of most chemicals, hydrocarbons and solvents
- Designed for indoor and outdoor applications

General

Catalog Number	NVZMFG26RBG
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Flashing
Material	Polyester, Fiberglass Reinforced
Optic Type	Polycarbonate Globe - Red
Series	NV
UPC	783936071275

Dimensions



Hub Size 3/4"

Electrical Ratings

Frequency Rating 50/60 Hz
Voltage Rating 12-80 VDC / 24 VAC

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Division 2, Groups F, G• Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

[Certifications - NVSL & NVSP Series CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Specifications - NVZMFG26RBG Specification Sheet French](#)
[Specifications - NVZMFG26RBG Specification Sheet English](#)
[Specifications - NVS Series Non-Metallic Corrosive Resitant Signals Specification Sheet](#)



A Hubbell brand