

By Killark  
Catalog # OC-3CG

O/Duraloy 5 Conduit Body with Cover And Gasket- C Type - Hub  
Size 1", 12.0 cu in



## Features

- Up to date with 419 and tapered hubs specifications
- Type 4 when used with neoprene gasket and cover
- Malleable iron suitable for use in concrete
- Interchangeable with competitive cover/gasket
- Staked stainless steel screws on stamped covers
- 1-1/4" - 4" LB and C hub configurations now available with rollers for relief of pulling conductors
- Killark K-Pak available which neatly packs cover and gasket together with displayed part number and UPC bar code store front displaying
- For conduit body packaged with cover and gasket, add CG to the catalog number

## Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

## Specifications

EU RoHS Indicator

Contact Manufacturer

## Configuration

Hub Pattern

C

## Dimensions

|                             |                       |
|-----------------------------|-----------------------|
| Hub Size                    | 1"                    |
| Length                      | 5 in                  |
| Gross Weight with Packaging | 0.68                  |
| Width                       | 10 in                 |
| Weight                      | 0.68 lb.              |
| Height                      | 0.1 in                |
| Dimensions                  | 5 in x 10 in x 0.1 in |

## General

|          |  |
|----------|--|
| Color    | Gray   |
| Type     | Conduit Body With Cover & Gasket             |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| UPC      | 783936049243                                 |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 20 |
|-----------------|----|



A Hubbell brand