



OC-4 - 1-1/4" C Hub, Aluminum O Series Conduit Body

By Killark
Catalog # [OC-4](#)

1-1/4" C Hub, Aluminum O Series Conduit Body



*Representative Image

Features

-
-
-
-
-

General

Catalog Number	OC-4
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	C
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
UPC	783936450049

Dimensions

Dimensions	10.25 in x 5 in x 5.5 in
Gross Weight with Packaging	1.4
Height	5.5 in
Hub Size	1-1/4"
Length	10.25 in
Weight	1.4 lb

Width5 in

Certifications And Compliance

CSA File Number	LR1852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Product Assets

- [3D Models - OC-4 3D Model](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - OC-4 Engineering Drawing](#)
- [Sales Drawings - OC-4 Sales Drawing](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OC4 Specification Sheet English](#)
- [Specifications - OC-4 Specification Sheet French](#)