



OC-9M - 3-1/2" C Hub, Iron O Series Conduit Body

By Killark
Catalog # [OC-9M](#)

3-1/2" C Hub, Iron O Series Conduit Body



*Representative Image

Features

-
-
-
-
-

General

Catalog Number	OC-9M
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	C
Material	Iron
Series	O Series
UPC	783936480237

Dimensions

Dimensions	19.25 in x 8.5 in x 5.5 in
Gross Weight with Packaging	20.03
Height	5.5 in
Hub Size	3-1/2"
Length	19.25 in

Width	8.5 in
-------	--------

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Certifications - Iron O-Series UL Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - OC-9M Specification Sheet French](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OC9M Specification Sheet English](#)