



# OL-45-RG - 1½" Neoprene O series Cover Gasket

By Killark  
Catalog # [OL-45-RG](#)

1½" Neoprene O series Cover Gasket



\*Representative Image

### Application

For use with O Series fittings.

### General

|                   |                      |
|-------------------|----------------------|
| Catalog Number    | OL-45-RG             |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type       | Powder Epoxy Paint   |
| Material          | Neoprene             |
| Series            | O Series             |
| Type              | Gasket               |
| UPC               | 783936490113         |

### Dimensions

|                             |                               |
|-----------------------------|-------------------------------|
| Dimensions                  | 10.12 in x 4.68 in x 7.062 in |
| Gross Weight with Packaging | 0.04                          |

|          |                  |
|----------|------------------|
| Height   | 7.062 in         |
| Hub Size | 1-1/4" to 1-1/2" |
| Length   | 10.12 in         |
| Weight   | 0.16 lb          |
| Width    | 4.68 in          |

### Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 25 |
|-----------------|----|

### Product Assets

- [Catalogs - Killark Catalog](#)
- [Specifications - OL45RG Specification Sheet English](#)
- [Specifications - OL-45-RG Specification Sheet French](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)