



OLB-3CG - O/Duraloy 5 Conduit Body with Cover And Gasket- LB Type - Hub Size 1",12.0 cu in

By Killark
Catalog # [OLB-3CG](#)



*Representative Image

O Series/Duraloy 5 Series Aluminum Conduit Body with Cover And Gasket- LB Type - Hub Size 1" - Volume 12.0 cu in

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OLB-3CG
Cover Type	Stamped
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LB
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	Conduit Body With Cover & Gasket
UPC	783936049274

Dimensions

Dimensions	5 in x 10 in x 0.1 in
------------	-----------------------

Gross Weight with Packaging	0.78
Height	0.1 in
Hub Size	1"
Length	5 in
Weight	0.78 lb
Width	10 in

Logistics

Carton Quantity	15
-----------------	----

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - OLB3CG Specification Sheet English](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OLB-3CG Specification Sheet French](#)