



OLB-6 - 2" LB Hub O Conduit Body

By Killark
Catalog # [OLB-6](#)

2" LB Hub O Series Conduit Body



*Representative Image

Features

-
-
-
-
-

General

Catalog Number	OLB-6
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LB
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
UPC	783936490304

Dimensions

Dimensions	10 in x 4 in x 5 in
Gross Weight with Packaging	2.05
Height	5 in
Hub Size	2"
Length	10 in
Weight	2.05 lb
Width	4 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [3D Models - OLB-6 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - OLB-6 Engineering Drawing](#)
- [Sales Drawings - OLB-6 Sales Drawing](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OLB6 Specification Sheet English](#)
- [Specifications - OLB-6 Specification Sheet French](#)