



OLB-6CG - O/Duraloy 5 Conduit Body with Cover And Gasket- LB Type - Hub Size 2",70.0 cu in

By Killark
Catalog # [OLB-6CG](#)



*Representative Image

O Series/Duraloy 5 Series Aluminum Conduit Body with Cover And Gasket- LB Type - Hub Size 2" - Volume 70.0 cu in

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OLB-6CG
Cover Type	Stamped
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LB
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	Conduit Body With Cover & Gasket
UPC	783936480053

Dimensions

Dimensions	1 in x 3 in x 3 in
------------	--------------------

Gross Weight with Packaging	2.8
Height	3 in
Hub Size	2"
Length	1 in
Weight	2.8 lb
Width	3 in

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OLB-6CG Specification Sheet French](#)
- [Specifications - OLB6CG Specification Sheet English](#)