



OLB-8MCG - O Series/Duraloy 5 Series - Malleable Iron Conduit Body With Cover And Gasket - LB Type - Hub Size 3 Inch - Volume 173.0 Cubic Inches

By Killark
Catalog # [OLB-8MCG](#)

O Series/Duraloy 5 Series - Malleable Iron Conduit Body With Cover And Gasket - LB Type - Hub Size 3 Inch - Volume 173.0 Cubic Inches

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OLB-8MCG
Color	Gray
Cover Type	Stamped
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LB
Material	Iron
Series	O Series
Type	Conduit Body With Cover & Gasket



*Representative Image

UPC 783936050089

Dimensions

Gross Weight with Packaging	14.96
Hub Size	3"

Product Assets

- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - OLB8MCG Specification Sheet English](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OLB-8MCG Specification Sheet French](#)



A Hubbell brand