



OLL-4 - 1 1/4" LL Hub O Conduit Body

By Killark
Catalog # [OLL-4](#)

1 1/4" LL Hub O Series Conduit Body



*Representative Image

Features

-
-
-
-
-

General

Catalog Number	OLL-4
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LL
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
UPC	783936490441

Dimensions

Dimensions	10.25 in x 5.125 in x 5.125 in
Gross Weight with Packaging	1.36
Height	5.125 in
Hub Size	1-1/4"
Length	10.25 in
Width	5.125 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Product Assets

- [3D Models - OLL-4 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - OLL-4 Engineering Drawing](#)
- [Sales Drawings - OLL-4 Sales Drawing](#)
- [Specifications - OLL-4 Specification Sheet French](#)
- [Specifications - OLL4 Specification Sheet English](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)