



OLL-4M - 1-1/4" LL Hub, Iron O Series Conduit Body

By Killark
Catalog # [OLL-4M](#)

1-1/4" LL Hub, Iron O Series Conduit Body



Features

- Raintight when used with gasketed covers.
- Malleable iron suitable for use in concrete.
- Interchangeable with competitive products.
- Stainless steel screws on stamped and cast covers.
- Tapered threaded hubs (NPT).

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Configuration

Hub Pattern LL

Dimensions

Hub Size	1-1/4"
Length	8.125 in
Gross Weight with Packaging	2.58
Width	3.5 in
Height	2.625 in
Dimensions	8.125 in x 3.5 in x 2.625 in

General

Series	O Series
Color	Gray
Type	Conduit Body
Material	Iron
UPC	783936480558

Logistics

Carton Quantity	2
Pallet Quantity	576

Product Assets

[Catalog \[English\]](#)