



OLR-2CG - O/Duraloy 5 Conduit Body with Cover And Gasket- LR Type - Hub Size 3/4",7.0 cu in

By Killark
Catalog # [OLR-2CG](#)



*Representative Image

O Series/Duraloy 5 Series Aluminum Conduit Body with Cover And Gasket- LR Type - Hub Size 3/4" - Volume 7.0 cu in

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OLR-2CG
Cover Type	Stamped
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LR
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	Conduit Body With Cover & Gasket
UPC	783936049328

Dimensions

Dimensions	15.5 in x 6 in x 9 in
------------	-----------------------

Gross Weight with Packaging	0.46
Height	9 in
Hub Size	3/4"
Length	15.5 in
Weight	0.46 lb
Width	6 in

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - OLR2CG Specification Sheet English](#)
- [Specifications - OLR-2CG Specification Sheet French](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)