



OLR-5M - 1-1/2" LR Hub, Iron O Series Conduit Body

By Killark
Catalog # [OLR-5M](#)



*Representative Image

1-1/2" LR Hub, Iron O Series Conduit Body

Features

-
-
-
-
-

General

Catalog Number	OLR-5M
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LR
Material	Iron
Series	O Series
UPC	783936480664

Dimensions

Dimensions	10 in x 5 in x 4 in
Gross Weight with Packaging	3.15
Height	4 in
Hub Size	1-1/2"
Length	10 in
Width	5 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Logistics

Carton Quantity	2
Pallet Quantity	576

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Certifications - Iron O-Series UL Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OLR5M Specification Sheet English](#)
- [Specifications - OLR-5M Specification Sheet French](#)