

OT-2CG - O/Duraloy 5 Conduit Body with Cover And Gasket- T Type - Hub Size 3/4", 7.0 cu in

By Killark

Catalog # [OT-2CG](#)

O Series/Duraloy 5 Series Aluminum Conduit Body with Cover And Gasket- T Type - Hub Size 3/4" - Volume 7.0 cu in

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OT-2CG
Cover Type	Stamped
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	T
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	Conduit Body With Cover & Gasket
UPC	783936049359

Dimensions

Dimensions 5 in x 10 in x 0.1 in



*Representative Image

Gross Weight with Packaging	0.47
Height	0.1 in
Hub Size	3/4"
Length	5 in
Weight	0.47 lb
Width	10 in

Logistics

Carton Quantity 25

Product Assets

[Catalogs - Killark Catalog](#)
[Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
[Customer Notices - Prop 65 Notice](#)
[Specifications - OT2CG Specification Sheet English](#)
[Specifications - OT-2CG Specification Sheet French](#)
[Specifications - O Series & Form 5 Cross Reference](#)
[Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)