



OT-3CG - O/Duraloy 5 Conduit Body with Cover And Gasket- T Type - Hub Size 1",12.0 cu in

By Killark
Catalog # **OT-3CG**

O/Duraloy 5 Conduit Body with Cover And Gasket- T Type - Hub Size 1",12.0 cu in



Features

- Up to date with 419 and tapered hubs specifications
- Type 4 when used with neoprene gasket and cover
- Malleable iron suitable for use in concrete
- Interchangeable with competitive cover/gasket
- Staked stainless steel screws on stamped covers
- 1-1/4" - 4" LB and C hub configurations now available with rollers for relief of pulling conductors
- Killark K-Pak available which neatly packs cover and gasket together with displayed part number and UPC bar code store front displaying
- For conduit body packaged with cover and gasket, add CG to the catalog number

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

Specifications

EU RoHS Indicator Contact Manufacturer

Configuration

Hub Pattern T

Dimensions

Hub Size	1"
Length	5 in
Gross Weight with Packaging	0.76
Width	10 in
Weight	0.76 lb.
Height	0.1 in
Dimensions	5 in x 10 in x 0.1 in

General

Color	Gray
Type	Conduit Body With Cover & Gasket
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936049366

Logistics

Carton Quantity	15
-----------------	----

Product Assets

[Catalog \[English\]](#)