



OT-4CG - O/Duraloy 5 Conduit Body with Cover And Gasket- T Type - Hub Size 1¼",32.0 cu in

By Killark
Catalog # [OT-4CG](#)



*Representative Image

O Series/Duraloy 5 Series Aluminum Conduit Body with Cover And Gasket- T Type - Hub Size 1¼" - Volume 32.0 cu in

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OT-4CG
Cover Type	Stamped
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	T
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	Conduit Body With Cover & Gasket
UPC	783936480121

Dimensions

Gross Weight with Packaging	1.55
Hub Size	1-1/4"

Logistics

Carton Quantity	8
-----------------	---

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OT-4CG Specification Sheet French](#)
- [Specifications - OT4CG Specification Sheet English](#)



A Hubbell brand