



OT-5 - 1-1/2" T Hub, Aluminum O Series Conduit Body

By Killark
Catalog # [OT-5](#)

1-1/2" T Hub, Aluminum O Series Conduit Body



*Representative Image

Features

-
-
-
-
-

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	OT-5
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	T
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
Type	Conduit Body
UPC	783936530055

Dimensions

Dimensions	10.375 in x 5 in x 5.375 in
Gross Weight with Packaging	1.65
Height	5.375 in
Hub Size	1-1/2"

Length	10.375 in
Weight	1.65 lb
Width	5 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Product Assets

- [3D Models - OT-5 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - OT-5 Engineering Drawing](#)
- [Sales Drawings - OT-5 Sales Drawing](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Specifications - OT5 Specification Sheet English](#)
- [Specifications - OT-5 Specification Sheet French](#)



A Hubbell brand