

## OT-6 - Manchon en T 2", corps de conduit en aluminium série O

Par Killark

No de catalogue OT-6



Moyeu en T de 2", corps de conduit en aluminium de la série O.

\*Image représentative

### Général

Numéro de catalogue	OT-6
Couleur	
Indicateur RoHS de l'UE	Contacter le fabricant
Type de finition	Peinture époxy en poudre
Modèle de moyeu	T
Matériau	Sans aluminium ni cuivre (moins de 4/10 de 1 %)
Série	Série O
Type	Conduit Body
CUP	783936530062

### Dimensions

Dimensions	10,5 po x 5 po x 5,125 po
Poids brut avec emballage	2.19
Hauteur	5,125 pouces
Taille du moyeu	2"
Longueur	10,5 pouces
Largeur	5 en

### Certifications et conformité

Numéro de dossier CSA	LR11852
Cote(s) de dangerosité	Convient aux applications en zone dangereuse lorsque l'installation est conforme aux articles 501.10(b) (Classe I, Division 2) ou 502.10, 503.10 et 505.15 (Classe I, Zone 2) du NEC.
Numéro de dossier UL	E3397

### Documentation

- [Avis aux clients - Prop 65 Notice](#)
- [Catalogues - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Dessin technique - OT-6 Engineering Drawing](#)
- [Dessins de vente - OT-6 Sales Drawing](#)
- [Modèles 3D - OT-6 3D Model](#)
- [Spécifications - OT-6](#)
- [Spécifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)
- [Spécifications - Conduit Fill Information](#)
- [Spécifications - O Series & Form 5 Cross Reference](#)