



OX-6 - 2" X Hub, Aluminum O Series Conduit Body

By Killark
Catalog # OX-6

2" X Hub, Aluminum O Series Conduit Body



*Representative Image

Features

-
-
-
-
-

General

Catalog Number	OX-6
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	X
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	O Series
UPC	783936550060

Dimensions

Dimensions	12 in x 6 in x 4 in
Gross Weight with Packaging	2.5
Height	4 in
Hub Size	2"
Length	12 in
Width	6 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [3D Models - OX-6 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - OX-6 Engineering Drawing](#)
- [Sales Drawings - OX-6 Sales Drawing](#)
- [Specifications - OX6 Specification Sheet English](#)
- [Specifications - OX-6 Specification Sheet French](#)
- [Specifications - O Series & Form 5 Cross Reference](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - O Series & Duraloy 5 Series Conduit Bodies Specification Sheet](#)