



# QL-1505K-WQ - QL Series - Aluminum 1500 Watt Quartz Floodlight (with Lamp) -1/2 Inch Swivel Knuckle

By Killark  
Catalog # [QL-1505K-WQ](#)



QL Series - Aluminum 1500 Watt Quartz Floodlight (with Lamp)  
-1/2 Inch Swivel Knuckle

### Features

- Tempered Glass Lens Assembly—Thermal shock-and impact-resistant glass lens mounted in a die cast aluminum door frame
- Cast Aluminum Housing—The cast aluminum body is designed with a specialized heat dissipating fin system for cooler operation
- Versatile Mounting—The standard unit has a 1/2 inch swivel knuckle with cast construction for strength and universal aiming
- Exclusive Socket System—This two piece, high temperature socket allows easy relamping and prevents socket from binding
- Reflector—Linear parabolic reflector system provides maximum light output
- High Temperature Gasketing—A weathertight seal is provided by a high temperature silicone gasket attached to the housing. Four lens clips positively seal the lens to the gasket with consistent pressure to assure a weathertight seal

### General

Catalog Number	QL-1505K-WQ
EU RoHS Indicator	Contact Manufacturer

Finish Type	Powder Epoxy Paint
Lamp Type	T3
Material	Aluminum
Optic Type	Glass Lens
Series	QL
UPC	783936562070

### Dimensions

Hub Size	1/2"
----------	------

### Electrical Ratings

Voltage Rating	240 VAC
Wattage	1500 W

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL\\_QL-1505K](#)
- [Specifications - QL1505KWQ Specification Sheet English](#)
- [Specifications - QL Series Quartz Floodlights Specification Sheet](#)
- [Specifications - QL-1505K-WQ Specification Sheet French](#)



A Hubbell brand