



T97 - 3-1/2" T Hub, Iron Form 7 Conduit Body

By Killark
Catalog # [T97](#)

3-1/2" T Hub, Iron Form 7 Conduit Body



*Representative Image

Features

- Enhanced sealing capabilities neoprene sealing gaskets provide a NEMA 3 Seal.
- Suitable for wet locations when used with gaskets.
- High-quality sealing hardware 316 stainless steel cover screws and washers with neoprene gaskets.
- Innovative spring clip design for installation ease and repeat usage.
- For use with threaded rigid conduit steel or aluminum.
- Flat-back design for greater wiring capacity and mounting stability.

General

Catalog Number	T97
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	T
Material	Iron
Series	Duraloy 7
UPC	783936011387

Dimensions

Dimensions	15 in x 8 in x 6 in
Gross Weight with Packaging	25
Height	6 in

Hub Size	3-1/2"
Length	15 in
Width	8 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Product Assets

- [3D Models - T97 3D Model](#)
- [Certifications - Duraloy 7 UL Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - T97 Engineering Drawing](#)
- [Installation Manuals - KIL_Duraloy 7 Series Conduit Bodies IOM_K1430](#)
- [Sales Drawings - T97 Sales Drawing](#)
- [Specifications - Duraloy 7 Series Conduit Bodies Specification Sheet](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - T97 Specification Sheet English](#)
- [Specifications - T97 Specification Sheet French](#)



A Hubbell brand