



UGFI Series 20A, 125VAC Portable GFCI Receptacle

By Killark
Catalog # [UGFI20AD](#)

20A, 125VAC Portable GFCI Receptacle



*Representative Image

General

Catalog Number	UGFI20AD
EU RoHS Indicator	Contact Manufacturer
Series	UGFI
UPC	783936660998

UL File Number	- Class I, Zone 2, Groups IIB+H2, IIA - Class II, Divisions 1 & 2, Groups F, G - Class III, Divisions 1 & 2 E91049
----------------	--

Dimensions

Weight	14 lb
--------	-------

Logistics

Carton Quantity	1
-----------------	---

Electrical Ratings

Amperage Rating	20
Voltage Rating	125 VAC

Product Assets

- [Installation Manuals - UGFI 1P Series Factory Sealed Portable GFCI Receptable IOM K1181](#)
- [Specifications - UGFI20AD Specification Sheet English](#)
- [Specifications - UGFI Series Ground Fault Protector Specification Sheet](#)
- [Specifications - UGFI20AD Specification Sheet French](#)

Certifications And Compliance

CSA File Number	LR14667
Hazardous Rating(s)	Class 1, Division 2, Groups B, C, D