



UGR Series 20A 250V Quick-Wire Acceptor Receptacle

By Killark
Catalog # [UGR0-20232QW](#)

20A 250V Quick-Wire Acceptor Receptacle



*Representative Image

Features

-
-
-
-
-
-

General

Catalog Number	UGR0-20232QW
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	2
Receptacle Type	Delayed Action
Series	UGR
UPC	783936125770

Electrical Ratings

Amperage Rating	20 A
-----------------	------

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
Nema Rating	3, 7(C, D), 9(F, G)

Logistics

Factory Sealed	Factory Sealed
----------------	----------------

Product Assets

- [Certifications - UGR/UGP Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_UGR,UGRQW Series Receptacles IOM_K1007](#)
- [Specifications - UGR0-20232QW Specification Sheet French](#)
- [Specifications - UGR020232QW Specification Sheet English](#)
- [Specifications - UGR & UGP Series Plugs & Receptacles Specification Sheet](#)