



UGRGF Series 20A, 125V GFI Protected Receptacle With Pilot Light, 3/4" Feed Thru

By Killark
Catalog # [UGRGF111-PL](#)

20A, 125V GFI Protected Receptacle With Pilot Light, 3/4" Feed Thru

Features

- Factory Sealed.
- Test and Reset push buttons are provided on cover assembly, with optional pilot light.
- Includes new GFCI to meet latest UL943 GFCI standards revisions.
- Exterior gasket provides NEMA 3 weatherproof protection.
- Ground boss for grounding in the splice box.
- Color coded wiring and stainless steel cover bolts.
- Receptacle used is UGR0-20231QW.
- Unit should be tested monthly.

General

Catalog Number	UGRGF111-PL
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2
Series	UGRGF
UPC	783936012742

Dimensions

Hub Size	3/4"
Weight	7.5 lb

Electrical Ratings



*Representative Image

Amperage Rating	20
Voltage Rating	125 VAC

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class 1, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups F, G• Class III, Divisions 1 & 2
Nema Rating	3, 7(C, D), 9(F, G)

Product Assets

[Certifications - UGRGF Series CSA Certificate of Compliance](#)
[Specifications - UGRGF111-PL Specification Sheet French](#)
[Specifications - UGRGF111PL Specification Sheet English](#)
[Specifications - UGRS & UGRGF Series Receptacles Specification Sheet](#)



A Hubbell brand