



# UGRS Series 20A 125V Square Receptacle Quick-Wire with Breech-Lock Cap

By Killark  
Catalog # [UGRS-20231BQW](#)

20A 125V Square Receptacle Quick-Wire with Breech-Lock Cap.



\*Representative Image

## Features

- Available with Exclusive Breech-Lock Lid
- Patented lid notch allows for screwdriver, etc. to hold open lid for easier, two-hand installation.
- Factory Sealed Construction
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- Dead Front Construction with Integral Switch - requires Hazardous Rated NEMA-Bladed Plug for operation
- Rotateable Design allows for installation flexibility

## General

Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	2
Receptacle Type	Delayed Action
Series	UGRS
Type	<ul style="list-style-type: none"> <li>• Straight Blade</li> <li>• Straight Blade</li> </ul>
UPC	783936124582

## Electrical Ratings

Amperage Rating	20 A
Current Rating	100 A

## Conductor Related

Number Of Wires	3
-----------------	---

## Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Division 2, Groups B, C, D</li> <li>• Class I, Zone 2, Groups IIB+H2, IIA</li> <li>• Class II, Divisions 1 &amp; 2, Groups F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)

## Logistics

Factory Sealed	Factory Sealed
----------------	----------------

## Product Assets

[3D Models - UGRS-20231BQW 3D Model \(STP\)](#)  
[Certifications - UGRP/UGRS Series Receptacles CSA Cert](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - KIL\\_UGRS, UGRS-QW Acceptor Series Square Mount Receptacle IOM\\_K1428](#)



A proud member of the Hubbell Family.