



UNF100 - Hazardous Location Union - Zinc Plated Steel - 1" Female/Female

By Killark
Catalog # [UNF100](#)

Hazardous Location Union - Zinc Plated Steel - 1" Female/Female.



Features

- Unique design offers a compact size for lighter weight and smaller profile for critical clearances with equipment
- Extruded bar stock construction provides superior threads over sand cast and provides twice the tensile strength
- Uniform design across all sizes for aesthetic and robust appeal
- Male to Female union has nonremovable nipple to ensure tight seal with union and pipe/equipment
- Made in the USA

General

Color	<ul style="list-style-type: none">• Silver• Silver
Finish Type	Plaqué zinc
Hex Size	1.69 in
Material	12L14 Steel
Series	UNF
Type	Union
UPC	783936184067

Dimensions

Diameter	1.75 in
Hub Size	1"
Length	1.81 in
Weight	0.4 lb

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	4

Product Assets

- [3D Models - UNF100 3D Model \(STP\)](#)
- [Certifications - UNF/UNY Series New Unions UL Certificate of Compliance](#)
- [Sales Drawings - UNF100 Sales Drawing \(PDF\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-UNF100-SPEC-EN | REV 1/2024