



# UNF125 - Hazardous Location Union - Zinc Plated Steel - 1-1/4" Female/Female

By Killark  
Catalog # [UNF125](#)

Hazardous Location Union - Zinc Plated Steel - 1-1/4" Female/Female.



## Features

- Unique design offers a compact size for lighter weight and smaller profile for critical clearances with equipment
- Extruded bar stock construction provides superior threads over sand cast and provides twice the tensile strength
- Uniform design across all sizes for aesthetic and robust appeal
- Male to Female union has nonremovable nipple to ensure tight seal with union and pipe/equipment
- Made in the USA

## General

Color	<ul style="list-style-type: none"><li>• Silver</li><li>• Silver</li></ul>
Finish Type	Zinc Plated
Hex Size	2.06 in
Material	12L14 Steel
Series	UNF
Type	<ul style="list-style-type: none"><li>• Female/Female Union</li><li>• Female/Female Union</li></ul>
UPC	783936184074

## Dimensions

Diameter	2.19 in
Hub Size	1-1/4"
Length	1.94 in
Weight	0.61 lb

## Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups A, B, C, D</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
Nema Rating	4

## Product Assets

- [3D Models - UNF125 3D Model \(STP\)](#)
- [Certifications - UNF/UNY Series New Unions UL Certificate of Compliance](#)
- [Sales Drawings - UNF125 Sales Drawing \(PDF\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-UNF125-SPEC-EN | REV 1/2024