

UNF2

By Killark
Catalog # UNF2

UN Series - Iron Union - Female/Female - Hub Size ¾"



*Representative Image

Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction

Application

UNF unions are used to connect two pieces of conduit or attach conduit to junction boxes, fittings, or devices. Permits removal of equipment without turning or removal of conduit.

General

Catalog Number	UNF2
EU RoHS Indicator	Contact Manufacturer
Finish Type	Zinc Plated
Material	Steel
Series	UNF
Type	Female to Female Union
UPC	783936010472

Dimensions

Dimensions	2 in x 2 in x 2 in
Gross Weight with Packaging	0.5
Height	2 in
Hub Size	¾"
Length	2 in
Weight	0.5 lb

Width	2 in
-------	------

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class I, Zones 1 & 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E10514

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Certifications - UNF/UNY Series Expansion Unions UL Certification](#)
- [Certifications - GUF/GUM Series Unions CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - UNF2 Specification Sheet French](#)
- [Specifications - UNF2 Specification Sheet English](#)
- [Specifications - UNF-UNY Series Expansion Unions Specification Sheet](#)
- [Specifications - GUF/GUM & UNF/UNY Series Unions Specification Sheet](#)