



UNY75 - Hazardous Location Union - Zinc Plated Steel - 3/4" Male/Female

By Killark
Catalog # [UNY75](#)

Hazardous Location Union - Zinc Plated Steel - 3/4"
Male/Female.



Features

- Unique design offers a compact size for lighter weight and smaller profile for critical clearances with equipment
- Extruded bar stock construction provides superior threads over sand cast and provides twice the tensile strength
- Uniform design across all sizes for aesthetic and robust appeal
- Male to Female union has nonremovable nipple to ensure tight seal with union and pipe/equipment
- Made in the USA

General

Color	<ul style="list-style-type: none">• Silver• Silver
Finish Type	Plaqué zinc
Hex Size	1.44 in
Material	12L14 Steel
Series	UNY
Type	Union
UPC	783936183954

Dimensions

Diameter	1.5 in
Hub Size	3/4"
Length	2.13 in
Weight	0.36 lb

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	4

Product Assets

- [3D Models - UNY75 3D Model \(STP\)](#)
- [Certifications - UNF/UNY Series New Unions UL Certificate of Compliance](#)
- [Sales Drawings - UNY75 Sales Drawing \(PDF\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-UNY75-SPEC-EN | REV 1/2024