



VBQ Series Hazardous Interlocked Receptacle - Square D - FHL Series 70A Breaker 3P 4W

By Killark
Catalog # [VBQ6034SH70](#)

Square D - FHL Series 60A Receptacle 70A Breaker 3W4P

Features

-
-
-
-
-
-
-

General

Catalog Number	VBQ6034SH70
EU RoHS Indicator	Contact Manufacturer
Hub Pattern	Dead-End
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	3
Receptacle Type	Mechanically Interlocked
Series	VBQ
UPC	783936835341

Dimensions

Hub Size	1-1/2"
----------	--------



Electrical Ratings

Amperage Rating	60 A
-----------------	------

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups B, C, D • Class I, Zone 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
Nema Rating	7 (C, D)

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VBQ Series Breaker Protected Receptacles Specification Sheet](#)
- [Specifications - VBQ6034SH70 Specification Sheet French](#)
- [Specifications - VBQ6034SH70 Specification Sheet English](#)