



VBQ Series Replacement Receptacle 30A 3P 4W

By Killark
Catalog # [VBQRA3034](#)

Versamate Replacement Receptacle 30A 3W4P.



Features

- Plug Interlock Mechanism for Dead-Front construction. Switch cannot be turned “ON” without fully inserted plug. Plug cannot be removed with switch in “ON” position
- Ground Fault Options Available
- Spacious wiring room that meets NEC wire bending requirements.
- Adjustable mounting lugs
- Quick Release Cover Bolts with Triple Leads for faster removal
- Electrostatically applied polyester/epoxy finish
- Breaker Handle has provisions for locking “ON” or “OFF” with up to three Padlocks

General

Catalog Number	VBQRA3034
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	3
Receptacle Type	Mechanically Interlocked
Series	VBQ
Type	
UPC	783936019352

Electrical Ratings

Amperage Rating	30 A
-----------------	------

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

Hazardous Rating(s)	Class I, Division 2, Groups B, C, D Class I, Zone 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups F, G Class III, Divisions 1 & 2
Nema Rating	3, 7(C, D), 9(F, G)

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-VBQRA3034-SPEC-EN | REV 6/2024