



VE3Q5226E30B2GLG - VE3 52W Normal/26W Emergency,120-277V, 3/4" Wall Mount,Globe with Guard

By Killark
Catalog # [VE3Q5226E30B2GLG](#)

VE3 52W Normal/26W Emergency,120-277V, 3/4" Wall
Mount,Globe with Guard

Features

-
-
-
-
-
-
-
-

General

Catalog Number	VE3Q5226E30B2GLG
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Lumen Range	2,001-5,000 lm
Lumens	3600
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Optic Type	Glass Globe - Clear
Series	VE3Q
UPC	783936114422

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------



Lumens Per Watt	69.2
Voltage Rating	120-277 VAC
Wattage	52 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Division 2, Groups F, G • Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

- [Certifications - VE Series CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_VEB,DEB,VEQ Fluorescent Luminaires IOM_K1207](#)
- [Photometry - KIL_VE3Q5226E30xxGL](#)
- [Photometry - KIL_VE3Q5226E30xxGL-A](#)
- [Photometry - KIL_VE3Q5226E30xxGL EM](#)
- [Photometry - KIL_VE3Q5226E30xxGL-S](#)
- [Photometry - KIL_VE3Q5226E30xxGL-S EM](#)
- [Photometry - KIL_VE3Q5226E30xxGL-A EM](#)
- [Specifications - VE3Q/VE4Q Series Compact Fluorescent Emergency Specification Sheet](#)
- [Specifications - VE3Q5226E30B2GLG Specification Sheet English](#)
- [Specifications - VE3Q5226E30B2GLG Specification Sheet French](#)