



VFBGG-2-200

By Killark
Catalog # [VFBGG-2-200](#)

200W V Series Incandescent 3/4" Wall Mount to VBC Splice Box with Guard.



Features

- Electrostatically applied epoxy/polyester finish
- Modular design
- Hubs are threaded for attachment to conduit
- Set screws in pendant fixture
- Copper-free aluminum (less than .004%)

General

Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Light Source	Incandescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Ceiling
Optic Type	Glass Globe - Clear
Series	V Series
UPC	783936824390

Dimensions

Hub Size 3/4"

Electrical Ratings

Frequency Rating 50/60 Hz
Voltage Rating 120-277 VAC
Wattage 300 W

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - KIL_V-Series Incandescent Luminaires IOM_K1153](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-VFBGG-2-200-SPEC-EN | REV 1/2024