



VFC-100 - V Series - V Fixture Body - Enclosed And Gasketed Fixture Body - 150W Maximum

By Killark
Catalog # [VFC-100](#)



V Series - V Fixture Body - Enclosed And Gasketed Fixture Body - 150W Maximum

Features

-
-
-
-
-

General

Catalog Number	VFC-100
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number of Lamps	0
Series	V Series
UPC	783936730011

Dimensions

Dimensions	1 in x 3 in x 3 in
Gross Weight with Packaging	0.5

Height	3 in
Length	1 in
Width	3 in

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	150 W

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_V-Series Incandescent Luminaires IOM_K1153](#)
- [Specifications - VFC-100 Specification Sheet French](#)
- [Specifications - VFC100 Specification Sheet English](#)
- [Specifications - V Series Incandescent Fixtures Specification Sheet](#)