



VM2LB7IE230 - VM2LB 7000

Lumen Range Standard with 2000 Lumen Battery Backup 120-277VAC 50/60 Hz

By Killark
Catalog # [VM2LB7IE230](#)



VM2LB 7000 Lumen Range Standard with 2000 Lumen Battery Backup 120-277VAC 50/60 Hz.

General

Catalog Number	VM2LB7IE230
Color Temperature	5000 K
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,001-10,000 lm
Lumens	7437
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Range Celcius	-20°C to +50°C
Series	VM2L
UPC	783936151724

Electrical Ratings

Lumens Per Watt	149
Voltage Rating	120-277 VAC
Wattage	50 W

Product Assets

[Customer Notices - Prop 65 Notice](#)