



VM2P150 - VM2 Series - 150W Pulse Start Metal Halide Quadri-Volt - Housing

By Killark
Catalog # [VM2P150](#)



VM2 Series - 150W Pulse Start Metal Halide Quadri-Volt - Housing

General

Catalog Number	VM2P150
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Light Source	Metal Halide Pulse
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Luminaire Only
Optic Type	Luminaire Only
Series	VM2
UPC	783936076409

- Class I, Zone 2, Groups IIC, IIB, IIA
- Class II, Divisions 1 & 2, Groups E, F, G
- Class III, Divisions 1 & 2

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	150 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D
---------------------	--

Product Assets

- [Certifications - VM1 & VM2 Series Luminaires CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_VM2P15xxxGL](#)
- [Photometry - KIL_VM2P15xxxER](#)
- [Photometry - KIL_VM2P15xxxGL-A](#)
- [Photometry - KIL_VM2P15xxxR1](#)
- [Photometry - KIL_VM2P15xxxR3](#)
- [Photometry - KIL_VM2P15xxxGL-D](#)
- [Photometry - KIL_VM2P15xxxR5](#)
- [Photometry - KIL_VM2P15xxxGL-S](#)
- [Specifications - VM2P150 Specification Sheet English](#)
- [Specifications - VM1/VM2 Series Specification Sheet](#)
- [Specifications - VM2P150 Specification Sheet French](#)