



VM3S155 - VM3 Series - 150W High Pressure Sodium 480V Housing

By Killark
Catalog # [VM3S155](#)

VM3 Series - 150W High Pressure Sodium 480V Housing.



General

Catalog Number	VM3S155
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Luminaire Only
Series	VM3
UPC	783936966106

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	480 VAC
Wattage	150 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">Class I, Division 2, Groups A, B, C, DClass I, Zone 2, Groups IIC, IIB, IIAClass II, Divisions 1 & 2, Groups E, F, GClass III, Divisions 1 & 2
---------------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Certifications - VM3 & VM4 Series Luminaires CSA Cert](#)
- [Certifications - VM3 & 4 Series Luminaires UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VM3/VM4 Series Mogul Base Specification Sheet](#)
- [Specifications - VM3S155 Specification Sheet French](#)