

## VM4LB07030 - VM4LB Series LED High Bay/ Low Bay, Hazardous Rated 70 Watt, 120-277 VAC 5000K, 8700 Lumens

By Killark

Catalog # [VM4LB07030](#)

The VM4L Series is a low bay and high bay fixture using energy efficient LED's. The design of the VM4LB with the bulb style heat sink creates a light distribution similar to a HID lamp. The design of the VM4LC with the concave style heat sink creates a light distribution with no up light. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. With the design of this fixtures internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins.

### Application

Certilite® V VM4L LED fixtures are designed for installations where moisture, dirt, dust, corrosion and vibration may be present, or NEMA 3 and 4X areas where wind, water, snow or high ambients can be expected. They can be used in locations made hazardous by the presence of flammable vapors or gases or combustible dusts as defined by the NEC/CEC

### General

|                   |                      |
|-------------------|----------------------|
| Catalog Number    | VM4LB07030           |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type       | Powder Epoxy Paint   |
| Light Source      | LED                  |
| Lumen Range       | 5,001-10,000 lm      |
| Lumens            | 9692                 |
| Mounting Type     | Luminaire Only       |
| Optic Type        | Luminaire Only       |
| Series            | VM4L                 |
| UPC               | 783936082547         |

### Electrical Ratings

|                  |             |
|------------------|-------------|
| Current Rating   | 100 A       |
| Frequency Rating | 50/60 Hz    |
| Lumens Per Watt  | 138.5       |
| Voltage Rating   | 120-277 VAC |



Wattage 70 W

### Certifications And Compliance

|                     |   |
|---------------------|---|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>Class I, Division 2, Groups A, B, C, D</li><li>Class I, Zone 2, Groups IIC, IIB, IIA</li><li>Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>Class III, Divisions 1 &amp; 2</li></ul> |
|---------------------|---|

### Logistics

Carton Quantity 1

### Product Assets

|  |
|--|
| Certifications - VM4L Series Luminaires CSA Cert                   |
| Certifications - VMLX/VM4L Series ATEX Certificate                 |
| Certifications - VMLX/VM4L Series EU Type ATEX Certificate         |
| Certifications - VMLX & VM4L Series IECEx Certification            |
| Customer Notices - Prop 65 Notice                                  |
| Installation Manuals - VM4L Series LED Luminaires IOM K1462        |
| Specifications - VM4LB07030 Specification Sheet French             |
| Specifications - VM4LB07030 Specification Sheet English            |
| Specifications - VM2L/VM4L Series High Wattage Specification Sheet |



A Hubbell brand