



# VM4S050 - VM4 Series - 50W High Pressure Sodium Quadri-Volt Housing

By Killark  
Catalog # [VM4S050](#)

VM4 Series - 50W High Pressure Sodium Quadri-Volt Housing.



## General

Catalog Number	VM4S050
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Luminaire Only
Series	VM4
UPC	783936966397

## Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	50 W

## Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
---------------------	---

## Product Assets

- [Certifications - VM3 & VM4 Series Luminaires CSA Cert](#)
- [Certifications - VM3 & 4 Series Luminaires UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VM3/VM4 Series Mogul Base Specification Sheet](#)
- [Specifications - VM4S050 Specification Sheet French](#)