



VM5S400 - VM5 Series, AL 400W High Wattage High Press Sodium Light Fixt (Lamp Not Incl), Optic Thread Size 7-3/4", Quadri-Volt(120/208/240/277V), 60Hz

By Killark
Catalog # [VM5S400](#)

VM5 Series - Aluminum 400 Watt High Wattage High Pressure Sodium Light Fixture (Lamp Not Included) - Optic Thread Size 7-3/4 Inch - Quadri-Volt(120/208/240/277V) At 60Hz.

General

Catalog Number	VM5S400
Color	<ul style="list-style-type: none"> Tan bronzer
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Mogul Base
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Luminaire Only
Reflector Type	Specular Aluminum
Series	VM5
Type	
UPC	783936966861

Dimensions

Dimensions	14.06 in x 14.88 in x 14 in
Gross Weight with Packaging	31
Height	14 in
Length	14.06 in
Width	14.88 in

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	400 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> Class I, Division 2, Groups A, B, C, D Class I, Zone 2, Groups IIC, IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Certifications - VM5 Series Luminaires CSA Cert](#)
- [Certifications - VM5 Series Luminaires UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_VM5S40xxxS5](#)
- [Photometry - KIL_VM5S40xxxS2](#)
- [Photometry - KIL_VM5S40xxxGL-A](#)
- [Photometry - KIL_VM5S40xxxER](#)
- [Photometry - KIL_VM5S40xxxGL-D](#)
- [Photometry - KIL_VM5S40xxxGL](#)
- [Photometry - KIL_VM5S40xxxGL-S](#)
- [Photometry - KIL_VM5S40xxxGL-Z](#)
- [Specifications - VM5 Series Mogul Base Specification Sheet](#)
- [Specifications - VM5S400 Specification Sheet French](#)