



VM5S405 - VM5 Series, AL 400 Watt High Wattage High Pressure Sodium Light Fixture (Lamp Not Included), Optic Thread Size 7-3/4", 480V, 60Hz

By Killark
Catalog # [VM5S405](#)



VM5 Series - Aluminum 400 Watt High Wattage High Pressure Sodium Light Fixture (Lamp Not Included) - Optic Thread Size 7-3/4 Inch - 480V At 60Hz.

General

Catalog Number	VM5S405
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Mogul Base
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Luminaire Only
Series	VM5
UPC	783936966878

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	480 VAC
Wattage	400 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Certifications - VM5 Series Luminaires CSA Cert](#)
- [Certifications - VM5 Series Luminaires UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_VM5S40xxxS5](#)
- [Photometry - KIL_VM5S40xxxS2](#)
- [Photometry - KIL_VM5S40xxxGL-A](#)
- [Photometry - KIL_VM5S40xxxER](#)
- [Photometry - KIL_VM5S40xxxGL-D](#)
- [Photometry - KIL_VM5S40xxxGL](#)
- [Photometry - KIL_VM5S40xxxGL-S](#)
- [Photometry - KIL_VM5S40xxxGL-Z](#)
- [Specifications - VM5 Series Mogul Base Specification Sheet](#)
- [Specifications - VM5S405 Specification Sheet French](#)