



# Versamate Series 100A 3 Pole 3 Wire Plug Assembly - AT Type

By Killark  
Catalog # [VP1033](#)

100A 3 Pole 3 Wire Plug Assembly - AT Type



\*Representative Image

## Features

- 
- 
- 
- 
- 
- 

## General

|                   |                                                                                                                                        |
|-------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number    | VP1033                                                                                                                                 |
| EU RoHS Indicator | Contact Manufacturer                                                                                                                   |
| Finish Type       | Baked Powder                                                                                                                           |
|                   | Epoxy/Polyester Finish                                                                                                                 |
| Grommet Range     | 0.88-1.68                                                                                                                              |
| Material          | Body-Copper-free aluminum;<br>Contacts-Brass; Spring<br>tensioner-Patented beryllium<br>copper; External screws-316<br>stainless steel |
| Series            | VersaMate                                                                                                                              |
| Style             | Style I                                                                                                                                |
| UPC               | 783936077604                                                                                                                           |

## Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 10.87 in x 4.25 in x 4.25 in |
| Height     | 4.25 in                      |
| Length     | 10.87 in                     |
| Width      | 4.25 in                      |

## Electrical Ratings

|                  |                                                                             |
|------------------|-----------------------------------------------------------------------------|
| Amperage Rating  | 100 A                                                                       |
| Frequency Rating | 50-400 Hz                                                                   |
| Voltage Rating   | <ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul> |

## Conductor Related

|                 |   |
|-----------------|---|
| Number Of Wires | 3 |
|-----------------|---|

## Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 100 Amp Allen Terminal IOM K1383](#)
- [Specifications - VP1033 Specification Sheet English](#)
- [Specifications - VP1033 Specification Sheet French](#)
- [Specifications - Versamate 100 AMP Replacement Parts Allen Terminal](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)