



Versamate Series 100A 3 Pole 4 Wire Plug Assembly - AT Type

By Killark
Catalog # [VP1034](#)

100A 3 Pole 4 Wire Plug Assembly - AT Type



*Representative Image

Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

General

Catalog Number	VP1034
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder Epoxy/Polyester Finish
Grommet Range	0.88-1.68
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936077703

Dimensions

Dimensions	10.87 in x 4.25 in x 4.25 in
Height	4.25 in
Length	10.87 in
Width	4.25 in

Electrical Ratings

Amperage Rating	100 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	3
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 100 Amp Allen Terminal IOM K1383](#)
- [Specifications - VP1034 Specification Sheet English](#)
- [Specifications - Versamate 100 AMP Replacement Parts Allen Terminal](#)
- [Specifications - VP1034 Specification Sheet French](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)



A Hubbell brand