



Versamate Series 100A 4 Pole 4 Wire Plug Assembly - AT Type

By Killark
Catalog # [VP1044](#)

100A 4 Pole 4 Wire Plug Assembly - AT Type



*Representative Image

Features

-
-
-
-
-
-

General

Catalog Number	VP1044
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Grommet Range	0.88-1.68
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style I
UPC	783936077666

Dimensions

Dimensions	10.87 in x 4.25 in x 4.25 in
Height	4.25 in
Length	10.87 in
Width	4.25 in

Electrical Ratings

Amperage Rating	100 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 100 Amp Allen Terminal IOM K1383](#)
- [Specifications - Versamate 100 AMP Replacement Parts Allen Terminal](#)
- [Specifications - VP1044 Specification Sheet French](#)
- [Specifications - VP1044 Specification Sheet English](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)