



# Versamate Series 200A 4 Pole 4 Wire Plug Assembly

By Killark  
Catalog # [VP204513](#)

200A 4 Pole 4 Wire Plug Assembly



\*Representative Image

### Features

- 
- 
- 
- 
- 
- 

### General

|                   |                                                                                                                                        |
|-------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number    | VP204513                                                                                                                               |
| EU RoHS Indicator | Contact Manufacturer                                                                                                                   |
| Finish Type       | Baked Powder                                                                                                                           |
|                   | Epoxy/Polyester Finish                                                                                                                 |
| Grommet Range     | 1.0-2.5                                                                                                                                |
| Material          | Body-Copper-free aluminum;<br>Contacts-Brass; Spring<br>tensioner-Patented beryllium<br>copper; External screws-316<br>stainless steel |
| Series            | VersaMate                                                                                                                              |
| Style             | Style I                                                                                                                                |
| UPC               | 783936833057                                                                                                                           |

### Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 12.62 in x 6.38 in x 6.38 in |
| Height     | 6.38 in                      |
| Length     | 12.62 in                     |
| Width      | 6.38 in                      |

### Electrical Ratings

|                  |                                                                             |
|------------------|-----------------------------------------------------------------------------|
| Amperage Rating  | 200 A                                                                       |
| Frequency Rating | 50-400 Hz                                                                   |
| Voltage Rating   | <ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul> |

### Conductor Related

|                 |   |
|-----------------|---|
| Number Of Wires | 4 |
|-----------------|---|

### Product Assets

- [Certifications - Versamate Series UL Certification](#)
- [Certifications - CSA Certificate - 200 Amp Versamate Series](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 200 Amp IOM K1206](#)
- [Specifications - VP204513 Specification Sheet French](#)
- [Specifications - VP204513 Specification Sheet English](#)
- [Specifications - Versamate 200 AMP Replacement Parts](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)