



Versamate Series 200A 3 Pole 4 Wire Plug Assembly

By Killark
Catalog # [VP204612](#)

200A 3 Pole 4 Wire Plug Assembly



*Representative Image

Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

General

Catalog Number	VP204612
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder Epoxy/Polyester Finish
Grommet Range	1.0-2.5
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936833064

Dimensions

Dimensions	12.62 in x 6.38 in x 6.38 in
Height	6.38 in
Length	12.62 in
Width	6.38 in

Electrical Ratings

Amperage Rating	200 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	3
-----------------	---

Product Assets

- [Certifications - Versamate Series UL Certification](#)
- [Certifications - CSA Certificate - 200 Amp Versamate Series](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 200 Amp IOM K1206](#)
- [Specifications - VP204612 Specification Sheet French](#)
- [Specifications - VP204612 Specification Sheet English](#)
- [Specifications - Versamate 200 AMP Replacement Parts](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)



A Hubbell brand