



Versamate Series 30A 2 Pole 3 Wire Plug Assembly - AT Type

By Killark
Catalog # [VP3023](#)

30A 2 Pole 3 Wire Plug Assembly - AT Type

Features

-
-
-
-
-
-

General

Catalog Number	VP3023
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder Epoxy/Polyester Finish
Grommet Range	0.55-1.20
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936077802

Dimensions



Dimensions	6.68 in x 3 in x 3 in
Height	3 in
Length	6.68 in
Weight	1.8 lb
Width	3 in

Electrical Ratings

Amperage Rating	30 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	2
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 30 Amp Allen Terminal IOM K1381](#)
- [Specifications - VP3023 Specification Sheet French](#)
- [Specifications - VP3023 Specification Sheet English](#)
- [Specifications - Versamate 30 AMP Replacement Parts Allen Terminal](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)