



Versamate Series 30A 4 Pole 4 Wire Plug Assembly - AT Type

By Killark
Catalog # [VP3044](#)

30A 4 Pole 4 Wire Plug Assembly - AT Type

Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

General

Catalog Number	VP3044
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Grommet Range	0.55-1.20
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style I
UPC	783936077833



Dimensions

Dimensions	6.68 in x 3 in x 3 in
Height	3 in
Length	6.68 in
Weight	1.81 lb
Width	3 in

Electrical Ratings

Amperage Rating	30 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 30 Amp Allen Terminal IOM K1381](#)
- [Specifications - VP3044 Specification Sheet French](#)
- [Specifications - VP3044 Specification Sheet English](#)
- [Specifications - Versamate 30 AMP Replacement Parts Allen Terminal](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)



A Hubbell brand