



## Versamate Series 30A 4 Pole 4 Wire Plug Assembly

By Killark  
Catalog # [VP3475](#)

30A 4 Pole 4 Wire Plug Assembly.



### General

Application	
Catalog Number	VP3475
EU RoHS Indicator	Contact Manufacturer
Finish Type	Finition époxy/polyester en poudre cuite
Grommet Range	0.55-1.20
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style I
Type	
UPC	783936834085

### Dimensions

Dimensions	6.68 in x 3 in x 3 in
Height	3 in
Length	6.68 in
Width	3 in

### Electrical Ratings

Amperage Rating	30 A
Frequency Rating	50-400 Hz
Voltage Rating	600 VAC
	250 VDC

### Conductor Related

Number Of Wires	2
-----------------	---

### Product Assets

[Certifications - CSA Certificate - 30 Amp Versamate Series](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Versamate 30 Amp Original Terminal IOM K1188](#)



A Hubbell brand